LT/SG1525A, LT/SG3525A
LT/SG1527A, LT/SG3527A

Regulating Pulse Width Modulators

FEATURES

- Undervoltage Lockout with Hysteresis
- *Guaranteed* 1% 5.1V Reference
- *Guaranteed* 10mV/1000 Hr Long Term Stability
- Latching PWM
- 8V to 35V Operation
- 100Hz to 400kHz Oscillator
- 400mA Source and Sink Current

APPLICATIONS

- Switching Power Supplies
- Motor Speed Control
- Power Converters

DESCRIPTION

The LT1525A and LT1527A are improved general purpose switching regulator control circuits. Included on the chip are a trimmed 1% voltage subsurface zener reference, oscillator, comparator and high current class B totem pole output drivers. Included in the design of the LT1525A are easy synchronization to an external clock, soft-start and adjustable deadtime control. A shutdown pin allows instantaneous shutdown.

The LT1525A and LT1527A differ only in their output logic phasing. The LT1525A has a low output during the "off" state, while the LT1527A has a high output during the "off" state. Both devices have undervoltage lockout with about 0.5V hysteresis, giving reliable operation even with slowly varying supplies.

The combination of improved features and advanced processing for high reliability make Linear Technology's switching regulators a supreme choice.

5

BLOCK DIAGRAM



LT1525A Start-Up



ABSOLUTE MAXIMUM RATINGS

(Note 1)

Supply Voltage ($+V_{IN}$) ..... +40V
Logic Inputs ..... −0.3V to +5.5V
Analog Inputs ..... −0.3V to $+V_{IN}$
Output Current, Source or Sink 500mA
Reference Output Current 50mA
Oscillator Charging Current 5mA
Power Dissipation at $T_A = +25°C$ (Note 2) ... 1000mW
Thermal Resistance: Junction to Ambient ... 100°C/W
Power Dissipation at $T_C = +25°C$ (Note 3) ... 2000mW
Thermal Resistance: Junction to Case ..... 60°C/W
Operating Temperature Range
1525A, 1527A ..... −55°C to 150°C
3525A, 3527A ..... 0°C to 70°C
Storage Temperature Range ..... −65°C to 150°C
Lead Temperature (Soldering, 10 sec.) ..... +300°C

PACKAGE/ORDER INFORMATION



ORDER PART NUMBER

LT1525AJ
LT1527AJ
LT3525AJ
LT3527AJ
LT3525AN
LT3527AN

SG1525AJ
SG1527AJ
SG3525AJ
SG3527AJ
SG3525AN
SG3527AN

RECOMMENDED OPERATING CONDITIONS

(Note 4)

Input Voltage ($+V_{IN}$) ..... +8V to +35V
Collector Supply Voltage (V_C) ..... +4.5V to +35V
Sink/Source Load Current
(Steady State) ..... 0mA to 100mA
Sink/Source Load Current (Peak) ..... 0mA to 400mA
Reference Load Current ..... 0mA to 20mA
Oscillator Frequency Range ..... 100Hz to 400kHz
Oscillator Timing Resistor ..... 2kΩ to 150kΩ
Oscillator Timing Capacitor ..... 0.001μF to 0.1μF
Deadtime Resistor Range ..... 0Ω to 500Ω

ELECTRICAL CHARACTERISTICS $V_{IN} = +20V$ unless otherwise noted

PARAMETER	CONDITIONS		LT1525A LT1527A			SG1525A SG1527A			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
REFERENCE SECTION									
Output Voltage	$T_j = 25°C$		5.05	5.10	5.15	5.05	5.10	5.15	V
Line Regulation	$V_{IN} = 8V$ to 35V	●		5	10		10	20	mV
Load Regulation	$I_L = 0mA$ to 20mA	●		20	50		20	50	mV
Temperature Stability		●		20	50		20	50	mV
Total Output Variation	Line, Load, and Temperature	●	5.0	5.1	5.2	5.0	5.1	5.2	V
Short Circuit Current	$V_{REF} = 0$, $T_j = 25°C$			80	100		80	100	mA
Output Noise Voltage	$10Hz \le f \le 10kHz$, $T_j = 25°C$			40	200		40	200	μVrms
Long Term Stability	$T_j = 125°C$			1	10		20	50	$mV/\sqrt{Khr}$

LINEAR TECHNOLOGY

ELECTRICAL CHARACTERISTICS

PARAMETER	CONDITIONS		LT1525A LT1527A			SG1525A SG1527A			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
OSCILLATOR SECTION (Note 6)									
Initial Accuracy	$T_j = 25°C$ (Note 6)			2	6		2	6	%
Voltage Stability	$V_{IN} = 8V$ to 35V	●		0 5	1		0.3	1	%
Temperature Stability		●		3	6		3	6	%
Minimum Frequency	$R_T = 150k\Omega$, $C_T = 0.1\mu F$	●			100			100	Hz
Maximum Frequency	$R_T = 2k\Omega$, $C_T = 1nF$	●	400			400			kHz
Current Mirror	$I_{RT} = 2mA$	●	1.7	2.0	2.2	1.7	2.0	2.2	mA
Clock Amplitude		●	3.0	3.5		3.0	3.5		V
Clock Width	$T_j = 25°C$		0.3	0.5	1	0.3	0.5	1	μs
Sync Threshold		●	1.2	2.0	2.8	1.2	2.0	2.8	V
Sync Input Current	Sync Voltage = 3.5V	●		1.0	2.5		1.0	2.5	mA
ERROR AMPLIFIER SECTION (V_{CM} = 5.1V)									
Input Offset Voltage		●		0.5	5		0.5	5	mV
Input Bias Current		●		0.2	3		1	10	μA
Input Offset Current		●			0.5			1	μA
DC Open Loop Gain	$R_L \geq 10M\Omega$	●	70	80		60	75		dB
Gain Bandwidth Product	$A_V = 0dB$, $T_j = 25°C$ (Note 5)		1	2		1	2		MHz
Output Low Level		●		0.2	0.5		0.2	0.5	V
Output High Level		●	3.8	5.6		3.8	5.6		V
Common Mode Rejection	$V_{CM} = 1.5V$ to 5.2V	●	75	90		60	75		dB
Supply Voltage Rejection	$V_{IN} = 8V$ to 35V	●	75	90		50	60		dB
PWM COMPARATOR									
Minimum Duty Cycle		●			0			0	%
Maximum Duty Cycle		●	45	49		45	49		%
Input Threshold	Zero Duty Cycle (Note 6)	●	0.6	0.9		0.6	0.9		V
Input Threshold	Max Duty Cycle (Note 6)	●		3.3	3.6		3.3	3.6	V
Input Bias Current		●		0.05	1.0		0.05	1.0	μA
SOFT-START SECTION									
Soft-Start Current	$V_{SHUTDOWN} = 0V$	●	25	50	80	25	50	80	μA
Soft-Start Voltage	$V_{SHUTDOWN} = 2V$	●		0.4	0.6		0.4	0.6	V
Shutdown Input Current	$V_{SHUTDOWN} = 2.5V$	●		0.4	1.0		0.4	1.0	mA
OUTPUT DRIVERS (Each Output) (V_C = 20V)									
Undervoltage Lockout Hysteresis			0.2	0.6	1	0.2	0.6	1	V
Output Low Level	$I_{SINK} = 20mA$	●		0.2	0.4		0.2	0.4	V
	$I_{SINK} = 100mA$	●		1.0	2.0		1.0	2.0	V
Output High Level	$I_{SOURCE} = 20mA$	●	18	19		18	19		V
	$I_{SOURCE} = 100mA$	●	17	18		17	18		V
Undervoltage Lockout	V_{COMP} and V_{SS} = High	●	6	7	8	6	7	8	V
Collector Leakage	$V_C = 35V$ (Note 7)	●			200			200	μA
Rise Time	$C_L = 1nF$, $T_j = 25°C$ (Note 5)			100	600		100	600	ns
Fall Time	$C_L = 1nF$, $T_j = 25°C$ (Note 5)			50	300		50	300	ns
Shutdown Delay	$V_{SD} = 3V$, $C_S = 0$, $T_j = 25°C$ (Note 5)			0.2	0.5		0.2	0.5	μs
TOTAL STANDBY CURRENT									
Supply Current	$V_{IN} = 35V$	●		14	20		14	20	mA

5

ELECTRICAL CHARACTERISTICS

PARAMETER	CONDITIONS		LT3525A LT3527A			SG3525A SG3527A			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
REFERENCE SECTION									
Output Voltage	$T_j = 25°C$		5.05	5.10	5.15	5.00	5.10	5.20	V
Line Regulation	$V_{IN} = 8V$ to 35V	●		5	10		10	20	mV
Load Regulation	$I_L = 0mA$ to 20mA	●		20	50		20	50	mV
Temperature Stability		●		20	50		20	50	mV
Total Output Variation	Line, Load, and Temperature	●	4.95	5.1	5.25	4.95		5.25	V
Short Circuit Current	$V_{REF} = 0$, $T_j = 25°C$			80	100		80	100	mA
Output Noise Voltage	$10Hz \leq f \leq 10kHz$, $T_j = 25°C$			40	100		40	200	μVrms
Long Term Stability	$T_j = 125°C$			1	10		20	50	mV/khr
OSCILLATOR SECTION (Note 6)									
Initial Accuracy	$T_j = 25°C$ (Note 6)			2	6		2	6	%
Voltage Stability	$V_{IN} = 8V$ to 35V	●		0.5	2		1	2	%
Temperature Stability		●		3	6		3	6	%
Minimum Frequency	$R_T = 150k\Omega$, $C_T = 0.1\mu F$	●			100			100	Hz
Maximum Frequency	$R_T = 2k\Omega$, $C_T = 1nF$	●	400			400			kHz
Current Mirror	$I_{RT} = 2mA$	●	1.7	2.0	2.2	1.7	2.0	2.2	mA
Clock Amplitude		●	3.0	3.5		3.0	3.5		V
Clock Width	$T_j = 25°C$		0.3	0.5	1.0	0.3	0.5	1.0	μs
Sync Threshold		●	1.2	2.0	2.8	1.2	2.0	2.8	V
Sync Input Current	Sync Voltage = 3.5V	●		1.0	2.5		1.0	2.5	mA
ERROR AMPLIFIER SECTION ($V_{CM} = 5.1V$)									
Input Offset Voltage		●		2	5		2	10	mV
Input Bias Current		●		1	3		1	10	μA
Input Offset Current		●			0.5			1	μA
DC Open Loop Gain	$R_L \geq 10M\Omega$	●	70	80		60	75		dB
Gain Bandwidth Product	$A_V = 0dB$, $T_j = 25°C$ (Note 5)		1	2		1	2		MHz
Output Low Level		●		0.2	0.5		0.2	0.5	V
Output High Level		●	3.8	5.6		3.8	5.6		V
Common Mode Rejection	$V_{CM} = 1.5V$ to 5.2V	●	75	90		60	75		dB
Supply Voltage Rejection	$V_{IN} = 8V$ to 35V	●	75	90		50	60		dB
PWM COMPARATOR									
Minimum Duty Cycle		●			0			0	%
Maximum Duty Cycle		●	45	49		45	49		%
Input Threshold	Zero Duty Cycle (Note 6)	●	0.6	0.9		0.6	0.9		V
Input Threshold	Max Duty Cycle (Note 6)	●		3.3	3.6		3.3	3.6	V
Input Bias Current		●		0.05	1.0		0.05	1.0	μA
SOFT-START SECTION									
Soft-Start Current	$V_{SHUTDOWN} = 0V$	●	25	50	80	25	50	80	μA
Soft-Start Voltage	$V_{SHUTDOWN} = 2V$	●		0.4	0.6		0.4	0.6	V
Shutdown Input Current	$V_{SHUTDOWN} = 2.5V$	●		0.4	1.0		0.4	1.0	mA

ELECTRICAL CHARACTERISTICS

PARAMETER	CONDITIONS		LT3525A LT3527A MIN	TYP	MAX	SG3525A SG3527A MIN	TYP	MAX	UNITS
OUTPUT DRIVERS (Each Output) (V_C = 20V)									
Undervoltage Lockout Hysteresis			0.2	0.6		0.2	0.6		V
Output Low Level	I_{SINK} = 20mA	●		0.2	0.4		0.2	0.4	V
	I_{SINK} = 100mA	●		1.0	2.0		1.0	2.0	V
Output High Level	I_{SOURCE} = 20mA	●	18	19		18	19		V
	I_{SOURCE} = 100mA	●	17	18		17	18		V
Undervoltage Lockout	V_{COMP} and V_{SS} = High	●	6	7	8	6	7	8	V
Collector Leakage	V_C = 35V (Note 7)	●			200			200	μA
Rise Time	C_L = 1nF, T_j = 25°C (Note 5)			100	600		100	600	ns
Fall Time	C_L = 1nF, T_j = 25°C (Note 5)			50	300		50	300	ns
Shutdown Delay	V_{SD} = 3V, C_S = 0, T_j = 25°C (Note 5)			0.2	0.5		0.2	0.5	μs
TOTAL STANDBY CURRENT									
Supply Current	V_{IN} = 35V	●		14	20		14	20	mA

The ● denotes the specifications which apply of the full operating temperature range.

Note 1: Values beyond which damage may occur.

Note 2: Derate at 10mW/°C for ambient temperatures above +50°C.

Note 3: Derate at 16mW/°C for case temperatures above +25°C.

Note 4: Range over which the device is functional and parameter limits are guaranteed.

Note 5: These parameters, although guaranteed over the recommended operating conditions, are not 100% tested in production.

Note 6: Tested at f_{OSC} = 40kHz (R_T = 3.6kΩ, C_T = 0.01μF, R_D = 0Ω).

Note 7: Applies to 1525A/3525A only, due to polarity of output pulses.

5

TYPICAL PERFORMANCE CHARACTERISTICS

Oscillator Charge Time vs R_T



Oscillator Discharge Time



Error Amplifier Open Loop Frequency Response



TYPICAL PERFORMANCE CHARACTERISTICS

1525A Output Saturation Characteristics



LT1527A Start-Up





1525A/1527A
C_L = 1kpF,
=5kpF,
=10kpF
V = 2.5V/DIV
H = 100ns/DIV



1525A/1527A
C_L = 1kpF,
=5kpF,
=10kpF
V = 2.5V/DIV
H = 100ns/DIV



OUTPUT CURRENT
100mA/DIV
100ns/DIV



OUTPUT CURRENT
100mA/DIV
100ns/DIV

APPLICATIONS INFORMATION

Shutdown Options

1. An external open collector comparator or transistor can be used to pull down the compensation pin (9). This will set the PWM latch and turn off both outputs. Pulse-by-pulse protection can be accomplished if the shutdown signal is momentary, since the PWM latch will be reset with each clock pulse.

2. Shutdown can also be accomplished by pulling down on the soft-start pin (8). When using this approach, shutdown will not affect the amplifier compensation network; however, if a soft-start capacitor is used, it must be discharged, possibly slowing shutdown response.

APPLICATIONS INFORMATION

3. Applying a positive-going signal to the shutdown pin (10) will provide the most rapid shutdown of the outputs if a soft-start capacitor is not used at pin 8. An external soft-start capacitor at pin 8 will slow shutdown response due to the discharge time of the soft-start capacitor. Discharge current is approximately twice the charging current.

4. The shutdown terminal can be used to set the PWM latch on a pulse-by-pulse basis if there is no external capacitance on pin 8. Soft-start characteristics may still be achieved by applying an external capacitor, blocking diode and charging resistor to the compensation pin (9).

TYPICAL APPLICATIONS

Single Ended Supply



FOR SINGLE ENDED SUPPLIES, THE DRIVER OUTPUTS ARE GROUNDED. THE $+V_C$ TERMINAL IS SWITCHED TO GROUND BY THE TOTEM-POLE SOURCE TRANSISTORS ON EVERY OSCILLATOR CYCLE.

Bipolar Push-Pull Supply



IN CONVENTIONAL PUSH-PULL BIPOLAR DESIGNS, FORWARD BASE DRIVE IS CONTROLLED BY R1–R3. RAPID TURN-OFF TIMES FOR THE POWER DEVICES ARE ACHIEVED WITH SPEED-UP CAPACITORS C1 AND C2.

Power FETs Push-Pull Supply



THE LOW SOURCE IMPEDANCE OF THE OUTPUT DRIVERS PROVIDES RAPID CHARGING OF POWER FET INPUT CAPACITANCE, WHILE MINIMIZING EXTERNAL COMPONENTS.

Driving Transformers Directly



LOW POWER TRANSFORMERS CAN BE DRIVEN DIRECTLY BY THE 1525A. AUTOMATIC RESET OCCURS DURING DEADTIME, WHEN BOTH ENDS OF THE PRIMARY WINDING ARE SWITCHED TO GROUND.

5

TEST CIRCUIT



PACKAGE DESCRIPTION

16 Pin Cavity DIP (J)



	$T_j$max	Θ_{jA}	Θ_{jC}
LT/SG1525AJ LT/SG1527AJ	150°C	100°C/W	60°C/W
LT/SG3525AJ LT/SG3527AJ	150°C	100°C/W	60°C/W

16 Pin Molded DIP (N)



	$T_j$max	Θ_{jA}	Θ_{jC}
LT/SG3525AN LT/SG3527AN	105°C	100°C/W	60°C/W

LINEAR TECHNOLOGY