AVX 83. 662. 314BC1



Dimensions of PC board holes (Commend)



Color layout

Circuit Diagram



Technical requirement:

1. This product should EU RoHS related requirement.
2. The surface of plastic part should be without any crackle such as burr , lack, and so on phenomenon.
3. The surface of metal part should be without any defectsuch as scaur, nick, oxidation and plating problem.
4. The electronic performance should be the same as spec.
5. The un-specified tolerance is :

	<6±0.1
	6-20±0.2
	>20±0.3

No:	Name	QTY	Material	Coat Cladding Material
6	Earthing Piece	1	QSn6.5-0.1 t=0.3	D.CuSn
5	Cover	1	ABS 94HB(Black)	———
4	Washer	3	ABS 94HB	———
3	Pincer Needle	3	QSn6.5-0.1 t=0.4	D.CuSn
2	Base	1	ABS 94HB(Black)	———
1	Outer Conductor	3	H65Brass t=0.4	D.CuSn

Number of Old Base Map					
Number of Base Map					
	Sign	Place Number	Changed document number	Signer	Date
Date / Signer	Designer	Dandan Yan	Standardization		
	Check	Yazhou Gao	Approved	Xiufeng Rao	
	Proofreader	Lixin Zhou			
	Process		Date	2007.4.16	

RS-334

3P RCA JACK

Design Mark	Weight	Scale
A		1.5:1

Total 1 Page | Page 1

DRAGON CITY INDUSTRIES LIMITED 龍豐實業有限公司