



Код продукта	Цвет изолятора	Сечение провода, кв. мм	d1, мм	d2, мм	L1, мм	L2, мм
TIC-0.25-6	голубой	0.25	0.75	1.90	10.00	6.00
TIC-0.25-8	голубой	0.25	0.75	1.90	12.00	8.00
TIC-0.34-6	зеленый	0.34	0.80	1.90	10.00	6.00
TIC-0.34-8	зеленый	0.34	0.80	1.90	12.00	8.00
TIC-0.50-6	белый	0.50	1.00	2.60	12.00	6.00
TIC-0.50-8	белый	0.50	1.00	2.60	14.00	8.00
TIC-0.50-10	белый	0.50	1.00	2.60	16.00	10.00
TIC-0.75-6	серый	0.75	1.20	2.80	12.00	6.00
TIC-0.75-8	серый	0.75	1.20	2.80	14.00	8.00
TIC-0.75-10	серый	0.75	1.20	2.80	16.00	10.00
TIC-0.75-12	серый	0.75	1.20	2.80	18.00	12.00
TIC-1.0-6	красный	1.00	1.40	3.00	12.00	6.00
TIC-1.0-8	красный	1.00	1.40	3.00	14.00	8.00
TIC-1.0-10	красный	1.00	1.40	3.00	16.00	10.00
TIC-1.0-12	красный	1.00	1.40	3.00	18.00	12.00
TIC-1.5-6	черный	1.50	1.70	3.50	12.00	6.00
TIC-1.5-8	черный	1.50	1.70	3.50	14.00	8.00
TIC-1.5-10	черный	1.50	1.70	3.50	16.00	10.00
TIC-1.5-12	черный	1.50	1.70	3.50	18.00	12.00
TIC-1.5-18	черный	1.50	1.70	3.50	24.00	18.00
TIC-2.5-8	синий	2.50	2.20	4.20	14.00	8.00
TIC-2.5-10	синий	2.50	2.20	4.20	16.00	10.00
TIC-2.5-12	синий	2.50	2.20	4.20	18.00	12.00
TIC-2.5-18	синий	2.50	2.20	4.20	24.00	18.00
TIC-4-10	серый	4.00	2.80	4.80	17.00	10.00
TIC-4-12	серый	4.00	2.80	4.80	20.00	12.00
TIC-4-18	серый	4.00	2.80	4.80	26.00	18.00
TIC-6-12	желтый	6.00	3.50	6.30	20.00	12.00
TIC-6-18	желтый	6.00	3.50	6.30	26.00	18.00
TIC-10-12	красный	10.00	4.50	7.60	22.00	12.00
TIC-10-18	красный	10.00	4.50	7.60	28.00	18.00
TIC-16-12	синий	16.00	5.80	8.80	24.00	12.00
TIC-16-18	синий	16.00	5.80	8.80	28.00	18.00
TIC-25-12	желтый	25.00	7.30	11.20	-	-
TIC-25-16	желтый	25.00	7.30	11.20	28.00	16.00
TIC-25-18	желтый	25.00	7.30	11.20	30.00	18.00
TIC-25-22	желтый	25.00	7.30	11.20	35.00	22.00
TIC-35-12	красный	35.00	8.30	12.70	26.00	12.00
TIC-35-16	красный	35.00	8.30	12.70	30.00	16.00
TIC-35-18	красный	35.00	8.30	12.70	32.00	18.00
TIC-35-25	красный	35.00	8.30	12.70	39.00	25.00
TIC-50-20	синий	50.00	10.30	15.00	36.00	20.00
TIC-50-25	синий	50.00	10.30	15.00	40.00	25.00
TIC-70-21	желтый	70.00	13.50	16.00	37.00	21.00
TIC-95-25	красный	95.00	14.70	18.00	44.00	25.00
TIC-120-27	синий	120.00	16.70	20.00	48.00	27.00
TIC-150-32	желтый	150.00	19.50	23.00	58.00	32.00