Bulletin PD-20606 rev. C 07/06

International
IOR Rectifier

30CTQ...
30CTQ...S
30CTQ...-1

SCHOTTKY RECTIFIER

30 Amp

$I_{F(AV)}$ = 30Amp
V_R = 80-100V

Major Ratings and Characteristics

Characteristics		Values	Units
$I_{F(AV)}$	Rectangular waveform	30	A
V_{RRM}		80 - 100	V
I_{FSM}	@ tp = 5 µs sine	850	A
V_F	@15 Apk, T_J = 125°C (per leg)	0.67	V
T_J	range	- 55 to 175	°C

Description/ Features

This center tap Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175°C junction temperature. Typical applications are in switching power supplies, converters, free-wheeling diodes, and reverse battery protection.

- 175° C T_J operation
- Center tap configuration
- Low forward voltage drop
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability

Case Styles

30CTQ...





TO-220

30CTQ... S



D^2PAK

30CTQ... -1



TO-262

Voltage Ratings

Parameters		30CTQ80 30CTQ80S 30CTQ80-1	30CTQ100 30CTQ100S 30CTQ100-1
V_R	Max. DC Reverse Voltage (V)	80	100
V_{RWM}	Max. Working Peak Reverse Voltage (V)		

Absolute Maximum Ratings

Parameters		Values	Units	Conditions	
$I_{F(AV)}$	Max. Average Forward (Per Leg)	15	A	50% duty cycle @ T_C = 129°C, rectangular wave form	
	Current * See Fig. 5 (Per Device)	30			
I_{FSM}	Max. Peak One Cycle Non-Repetitive	850	A	5µs Sine or 3µs Rect. pulse	Following any rated load condition and with rated V_{RRM} applied
	Surge Current (Per Leg) * See Fig. 7	275		10ms Sine or 6ms Rect. pulse	
E_{AS}	Non-Repetitive Avalanche Energy (Per Leg)	7.50	mJ	T_J = 25 °C, I_{AS} = 0.50 Amps, L = 60 mH	
I_{AR}	Repetitive Avalanche Current (Per Leg)	0.50	A	Current decaying linearly to zero in 1 µsec Frequency limited by T_J max. V_A = 1.5 x V_R typical	

Electrical Specifications

Parameters		Values	Units	Conditions	
V_{FM}	Max. Forward Voltage Drop	0.86	V	@ 15A	T_J = 25 °C
	(Per Leg) * See Fig. 1 (1)	1.05	V	@ 30A	
		0.67	V	@ 15A	T_J = 125 °C
		0.82	V	@ 30A	
I_{RM}	Max. Reverse Leakage Current	0.55	mA	T_J = 25 °C	V_R = rated V_R
	(Per Leg) * See Fig. 2 (1)	7.0	mA	T_J = 125 °C	
C_T	Max. Junction Capacitance (Per Leg)	500	pF	V_R = 5V_{DC} (test signal range 100Khz to 1Mhz) 25°C	
L_S	Typical Series Inductance (Per Leg)	8.0	nH	Measured lead to lead 5mm from package body	
dv/dt	Max. Voltage Rate of Change (Rated V_R)	10000	V/ µs		

(1) Pulse Width < 300µs, Duty Cycle <2%

Thermal-Mechanical Specifications

Parameters			Values	Units	Conditions
T_J	Max. Junction Temperature Range		-55 to 175	°C	
T_{stg}	Max. Storage Temperature Range		-55 to 175	°C	
R_{thJC}	Max. Thermal Resistance Junction to Case (Per Leg)		3.25	°C/W	DC operation
R_{thJC}	Max. Thermal Resistance Junction to Case (Per Package)		1.63	°C/W	DC operation
R_{thCS}	Typical Thermal Resistance, Case to Heatsink		0.50	°C/W	Mounting surface, smooth and greased (only for TO-220)
wt	Approximate Weight		2 (0.07)	g (oz.)	
T	Mounting Torque	Min.	6 (5)	Kg-cm (lbf-in)	
		Max.	12 (10)		



Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)



Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)



Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)



Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)



Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)



Fig. 6 - Forward Power Loss Characteristics (Per Leg)



Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)



Fig. 8 - Unclamped Inductive Test Circuit

(2) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$;
Pd = Forward Power Loss = $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);
Pd_{REV} = Inverse Power Loss = $V_{R1} \times I_R (1 - D)$; $I_R @ V_{R1} = 10\,V$

Outline Table



SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	3.56	4.83	.140	.190	
A1	0.51	1.40	.020	.055	
A2	2.03	2.92	.080	.115	
b	0.38	1.01	.015	.040	
b1	0.38	0.97	.015	.038	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.36	0.61	.014	.024	
c1	0.36	0.56	.014	.022	5
D	14.22	16.51	.560	.650	4
D1	8.38	9.02	.330	.355	
D2	11.68	12.88	.460	.507	7
E	9.65	10.67	.380	.420	4,7
E1	6.86	8.89	.270	.350	7
E2	-	0.76	-	.030	8
e	2.54 BSC		.100 BSC		
e1	5.08 BSC		.200 BSC		
H1	5.84	6.86	.230	.270	7,8
L	12.70	14.73	.500	.580	
L1	-	6.35	-	.250	3
øP	3.54	4.08	.139	.161	
Q	2.54	3.42	.100	.135	

Conform to JEDEC outline TO-220AB



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
5. CONTROLLING DIMENSION: INCH.

SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	4.06	4.83	.160	.190	
A1	0.00	0.254	.000	.010	
b	0.51	0.99	.020	.039	
b1	0.51	0.89	.020	.035	4
b2	1.14	1.78	.045	.070	
c	0.38	0.74	.015	.029	
c1	0.38	0.58	.015	.023	4
c2	1.14	1.65	.045	.065	
D	8.51	9.65	.335	.380	3
D1	6.86		.270		
E	9.65	10.67	.380	.420	3
E1	6.22		.245		
e	2.54 BSC		.100 BSC		
H	14.61	15.88	.575	.625	
L	1.78	2.79	.070	.110	
L1		1.65		.065	
L2	1.27	1.78	.050	.070	
L3	0.25 BSC		.010 BSC		
L4	4.78	5.28	.188	.208	
m	17.78		.700		
m1	8.89		.350		
n	11.43		.450		
o	2.08		.082		
p	3.81		.150		
R	0.51	0.71	.020	.028	
θ	90°	93°	90°	93°	

LEAD ASSIGNMENTS

HEXFET

1.- GATE
2, 4.- DRAIN
3.- SOURCE

IGBTs, CoPACK

1.- GATE
2, 4.- COLLECTOR
3.- EMITTER

DIODES

1.- ANODE *
2, 4.- CATHODE
3.- ANODE

* PART DEPENDENT.

Conform to JEDEC outline D^2Pak (SMD-220)
Dimensions in millimeters and (inches)

Outline Table



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION: INCH.
7. – OUTLINE CONFORM TO JEDEC TO-262 EXCEPT A1(max.), b(min.) AND D1(min.) WHERE DIMENSIONS DERIVED THE ACTUAL PACKAGE OUTLINE.

SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	4.06	4.83	.160	.190	
A1	2.03	3.02	.080	.119	
b	0.51	0.99	.020	.039	
b1	0.51	0.89	.020	.035	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.38	0.74	.015	.029	
c1	0.38	0.58	.015	.023	5
c2	1.14	1.65	.045	.065	
D	8.38	9.65	.330	.380	3
D1	6.86	–	.270	–	4
E	9.65	10.67	.380	.420	3,4
E1	6.22	–	.245		4
e	2.54 BSC		.100 BSC		
L	13.46	14.10	.530	.555	
L1	–	1.65	–	.065	4
L2	3.56	3.71	.140	.146	

LEAD ASSIGNMENTS

HEXFET
1.– GATE
2.– DRAIN
3.– SOURCE
4.– DRAIN

IGBTs, CoPACK
1.– GATE
2.– COLLECTOR
3.– EMITTER
4.– COLLECTOR

Modified JEDEC outline TO-262
Dimensions in millimeters and (inches)

Tape & Reel Information



Ao	10.50 +/– 0.1
Bo	15.80 +/– 0.1
B2	10.25 +/– 0.1
Ko	4.90 +/– 0.1
F	11.50 +/– 0.1
P1	16.00 +/– 0.1
W	24.00 +/– 0.3

NOTES:
1.0 10 SPROCKET HOLE PITH CUMULATIVE TOLERANCE ±.02
2.0 CAMBER NOT TO EXCEED 1mm In 100mm
3.0 MATERIAL: CONDUCTIVE BLACK STYRENIC ALLOY
4.0 Ko MEASURED FROM A PLANE ON THE INSIDE BOTTOM OF THE POCKET TO THE TOP SURFACE OF THE CARRIER
5.0 MEASURED FROM CENTRELINE OF SPROCKET HOLE TO CENTRELINE OF POCKET
6.0 VENDOR: (OPTIONAL)
7.0 MUST ALSO MEET REQUIREMENTS OF EIA STANDAR #EIA-481A TAPING OF SURFACE MOUNT COMPONENTS FOR AUTOMATIC PLACEMENT
8.0 SURFACE RESISTIVITY OF MOLDED MATL. MUST MEASURE LESS OR EQUAL TO 10^6 OHMS PER SQUARE. MEASURED IN ACCORDANCE TO PROCEDURE GIVEN IN ASTM D-257 & ASTM D-991
9.0 TOTAL LENGTH PER REEL MUST BE 45 METERS
10.0 © CRITICAL

Dimensions in millimeters and (inches)

Part Marking Information

TO-220

EXAMPLE: THIS IS A 30CTQ100
LOT CODE 1789
ASSEMBLED ON WW 19, 2000
IN THE ASSEMBLY LINE "C"



D²PAK

EXAMPLE: THIS IS A 30CTQ100S
LOT CODE 8024
ASSEMBLED ON WW 02, 2003
IN ASSEMBLY LINE "C"



TO-262

EXAMPLE: THIS IS A 30CTQ100-1
LOT CODE 1789
ASSEMBLED ON WW 19, 2002
IN ASSEMBLY LINE "C"



Ordering Information Table

Device Code



1	-	Current Rating (30A)
2	-	Circuit Configuration C = Common Cathode
3	-	T = TO-220
4	-	Schottky "Q" Series
5	-	Voltage Ratings — 080 = 80V, 100 = 100V
6	-	• S = D^2Pak • -1 = TO-262
7	-	• none = Tube (50 pieces) • TRL = Tape & Reel (Left Oriented - for D^2Pak only) • TRR = Tape & Reel (Right Oriented - for D^2Pak only)
8	-	• none = Standard Production • PbF = Lead-Free

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
Visit us at www.irf.com for sales contact information. 07/06