SEMICONDUCTOR

TOSHIBA

TECHNICAL DATA

TOSHIBA PHOTOCOUPLER

TLP3061, TLP3062, TLP3063

GaAs IRED & PHOTO-TRIAC

(TLP3061)

OFFICE MACHINE

HOUSEHOLD USE EQUIPMENT

TRIAC DRIVER

SOLID STATE RELAY

The TOSHIBA TLP3061, TLP3062 and TLP3063 consist of a zero voltage crossing turn-on photo-triac optically coupled to a gallium arsenide infrared emitting diode in a six lead plastic DIP package.

- Peak Off-State Voltage : 600V (Min.)
- Trigger LED Current : 15mA (Max.) (TLP3061)
  10mA (Max.) (TLP3062)
  5mA (Max.) (TLP3063)
- On-State Current : 100mA (Max.)
- UL Recognized : UL1577, File No. E67349
  Isolation Voltage : 5000Vrms (Min.)
- Option (D4) type
  VDE Approved : DIN VDE0884/08.87,
  Certificate No. 68329

  Maximum Operating Insulation Voltage : 630VPK
  Highest Permissible Over Voltage : 6000VPK

(Note) When a VDE0884 approved type is needed, please designate the "Option (D4)"

		7.62mm pich standard type	10.16mm pich (LF2) type
Creepage Distance	:	7.0mm (Min.)	8.0mm (Min.)
Clearance	:	7.0mm (Min.)	8.0mm (Min.)
Insulation Thickness	:	0.5mm (Min.)	0.5mm (Min.)

Unit in mm



JEDEC	—
EIAJ	—
TOSHIBA	11-9A2

Weight : 0.44g

PIN CONFIGURATION (TOP VIEW)



1 : ANODE
2 : CATHODE
3 : N.C.
4 : TERMINAL 1
6 : TERMINAL 2

www.alkom.net
(812) 560-03-27

© The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.

© These TOSHIBA products are intended for use in general commercial applications (office equipment, communication equipment, measuring equipment, domestic appliances, etc.). please make sure that you consult with us before you use these TOSHIBA products in equipment which requires extraordinarily high quality and/or reliability, and in equipment which may involve life threatening or critical application, including but not limited to such uses as atomic energy control, airplane or spaceship instrumentation, traffic signals, medical instrumentation, combustion control, all types of safety devices, etc. TOSHIBA cannot accept and hereby disclaims liability for any damage which may occur in case the TOSHIBA products are used in such equipment or applications without prior consultation with TOSHIBA.

(TLP3061)

MAXIMUM RATINGS (Ta = 25°C)

	CHARACTERISTIC		SYMBOL	RATING	UNIT
LED	Forward Current		I_F	50	mA
	Forward Current Derating (Ta ≧ 53°C)		ΔI_F / °C	−0.7	mA / °C
	Peak Forward Current (100 μs pulse, 100pps)		I_{FP}	1	A
	Power Dissipation		P_D	100	mW
	Power Dissipation Derating (Ta ≧ 25°C)		ΔP_D / °C	−1.0	mW / °C
	Reverse Voltage		V_R	5	V
	Junction Temperature		T_j	125	°C
DETECTOR	Off-State Output Terminal Voltage		V_{DRM}	600	V
	On-State RMS Current	Ta = 25°C	I_T (RMS)	100	mA
		Ta = 70°C		50	
	On-State Current Derating (Ta ≧ 25°C)		ΔI_T / °C	−1.1	mA / °C
	Peak On-State Current (100 μs pulse, 120pps)		I_{TP}	2	A
	Peak Nonrepetitive Surge Current (P_W = 10ms, DC = 10%)		I_{TSM}	1.2	A
	Power Dissipation		P_D	300	mW
	Power Dissipation Derating (Ta ≧ 25°C)		ΔP_D / °C	−4.0	mW / °C
	Junction Temperature		T_j	115	°C
Storage Temperature Range			T_{stg}	−55~150	°C
Operating Temperature Range			T_{opr}	−40~100	°C
Lead Soldering Temperature (10s)			T_{sol}	260	°C
Total Package Power Dissipation			P_T	330	mW
Total Package Power Dissipation Derating (Ta ≧ 25°C)			ΔP_T / °C	−4.4	mW / °C
Isolation Voltage (AC, 1min., R.H. ≦ 60%) (Note 1)			BV_S	5000	Vrms

Note 1 : Device considered a two terminal device : Pins 1, 2 and 3 shorted together and pins 4 and 6 shorted together.

www.dkonnet 十 (81) 560-03-27

(TLP3061)

INDIVIDUAL ELECTRICAL CHARACTERISTICS (Ta = 25°C)

	CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
LED	Forward Voltage	V_F	I_F = 10mA	1.0	1.15	1.3	V
	Reverse Current	I_R	V_R = 5V	—	—	10	μA
	Capacitance	C_T	V = 0, f = 1MHz	—	10	—	pF
DETECTOR	Peak Off-State Current	I_{DRM}	V_{DRM} = 600V	—	10	1000	nA
	Peak On-State Voltage	V_{TM}	I_{TM} = 100mA	—	1.7	3.0	V
	Holding Current	I_H	—	—	0.6	—	mA
	Critical Rate of Rise of Off-State Voltage	dv / dt	V_{in} = 240Vrms, Ta = 85°C (Fig.1)	200	500	—	V / μs
	Critical Rate of Rise of Commutating Voltage	dv / dt (c)	V_{in} = 60Vrms, I_T = 15mA (Fig.1)	—	0.2	—	V / μs

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Trigger LED Current	TLP3061	I_{FT}	V_T = 6V	—	—	15	mA
	TLP3062			—	5	10	
	TLP3063			—	—	5	
Inhibit Voltage		V_{IH}	I_F = Rated I_{FT}	—	—	50	V
Leakage in Inhibited State		I_{IH}	I_F = Rated I_{FT}, V_T = Rated V_{DRM}	—	100	300	μA
Capacitance Input to Output		C_S	V_S = 0, f = 1MHz	—	0.8	—	pF
Isolation Resistance		R_S	V_S = 500V (R.H. ≦ 60%)	5×10^{10}	10^{14}	—	Ω
Isolation Voltage		BV_S	AC, 1 minute	5000	—	—	Vrms
			AC, 1 second, in oil	—	10000	—	
			DC, 1 minute, in oil	—	10000	—	V_{dc}

RECOMMENDED OPERATING CONDITIONS

CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply Voltage	V_{AC}	—	—	240	Vac
Forward Current	I_F*	15	20	25	mA
Peak On-State Current	I_{TP}	—	—	1	A
Operating Temperature	T_{opr}	−25	—	85	°C

* In the case of TLP3062

Fig. 1 dv / dt TEST CIRCUIT



www.cnkon.net (812) 560-03-27

(TLP3061)

I_F – Ta



$I_{T\,(RMS)}$ – Ta



I_{FP} – D_R



I_F – V_F



$\Delta V_F / \Delta Ta$ – I_F



I_{FP} – V_{FP}



www.datasheet.net/ 1(812) 560-03-27

(TLP3061)

NORMALIZED I_{FT} – Ta



NORMALIZED I_H – Ta



NORMALIZED I_{DRM} – Ta



NORMALIZED I_{DRM} – Ta



NORMALIZED V_{IH} – Ta



NORMALIZED I_{IH} – Ta



www.alldatasheet.net +7 (812) 560-03-27